


Water gauge gaskets

for water gauge

AT 7063, 7065, 7066, 7067,
7068, 7069

Internet_Description

Internet_Variants



AT 7063

7063

Designation	Gauge size q ₃	DN	Dimenions	Approved for		
				kvm	vvm	AT no
Compression gasket for the adjustable sleeve inlet in the Armatec console AT 7358 in NBR-rubber	4	20	30x24x4	X	X	7063-20
	10	25	39x30x4	X	X	7063-25
	16	40	56x47x5	X	X	7063-40
Slide ring to the adjustable sleeve	4					7063R20
	10					7063R25
	16					7063R40

Designation	Gauge size q ₃	DN	Dimensions	AT no
O-ring in EPDM-rubber to extension piece for cold water meter AT 7055-20-30	4	20		7065-20
Flat gasket in leather for cold water meter impregnated with carnauba wax	4	20	29x23x3	7066-20
	10	25	38x29x3	7066-25
	16	40	55x43x3,5	7066-40
To 30 mm extension piece with release ring	4	20	30x21x3	7066-20S
Flat gasket in plastic (cross-linked polyethylene)	4	20	30x23x2	7067A20
- By check valve AT 7059	4	20	30x23x4	7067-20-4
	10	25	38x29x2	7067-25
	10	25	38x29x4	7067-25-4
	16	40	55x43x2	7067-40
	16	40	55x43x4	7067-40-4

Water gauge gaskets

for water gauge

AT 7063, 7065, 7066, 7067,
7068, 7069

Designation	Gauge size q_3	DN	Dimension	AT no
Flat gasket in fiber material for warm and hot water gauge (warm water) max 130°C	0,6-1,5	15	24x17x2	7068-15
	1,5 (AT 7080 80 mm)	15		7068-15S
	1,5-2,5	20	29x23x3	7068-20
	6	25	38x29x3	7068-25
	10	40	55x43x3	7068-40
Flat gasket (Klinger sieve) to transmission pieces q_n 2,5 and extension piece AT 7055-20-55/85/115	2,5	20	30x23x3	7068-20F
Flat gasket in NBR-rubber to cold and warm water max 90°C	2,5	20	30x23x3	7069-20
	2,5	20	30x23x2	7069-20-2
	5-6	25	38x29x2	7069-25
	5-6	25	38x29x3	7069-25-3
	10	40	55x43x3,5	7069-40
Flat gasket in NBR-rubber rubber with enlarged dimensions to 30 mm extension piece with release ring	2,5	20	32x23x3	7069-20S
Flat gasket, armed		50		7069- 50
NR-rubber, Flange gasket		65		7069- 65
		80		7069- 80
		100		7069-100
		150		7069-150
		200		7069-200

Rätten till ändringar utan föregående meddelande förbehålls.
Armatec ansvarar inte för eventuella tryckfel eller misstänksänd.
Dokumentet får kopieras endast i sin helhet.